



Veeder-Root

125 Powder Forest Drive
 P. O. Box 2003
 Simsbury, CT 06070-7684
 USA
 Phone: (860) 651-2700
 Fax: (860) 651-2719

To: Veeder-Root ATG customers
 From: Jeff Kappler, ATG Product Manager
 Date: October 7th, 2013
 Re: Biodiesel compatibility

The products listed in the table below are compatible with the alternative fuels as shown. TLS-450/350/300/2 tank gauge systems can be combined with any of these products to monitor the alternative fuels listed.

Equipment Type	Series or P/N	ASTM D6751 Biodiesel	Ethanol	Methanol
Magnetostrictive Probes (Aluminum)	Series 8463x0, 8473x0	0-20%	0-15%	0-7%
Magnetostrictive Probes (Stainless Steel)	Series 8463x1, 8473x1	0-100%	0-100%	0-100%
Continuous Interstitial Tank System	P/N 857280-100, -200, -30x	0-20%	0-15%	0-5%
Electronic Line Leak Detector	Series 8475, 8484, 8494	0-20%	0-15%	0-5%
Groundwater Monitoring	P/N 794380-621, -622, -624	0-20%	0-15%	0-5%
Interstitial Detectors	P/N 794380-xxx P/N 794390-xxx P/N 847990-001, -002 P/N 857060-xxx P/N 857080-xxx	0-20%	0-15%	0-5%
Vapor Monitoring	P/N 394390-700	0-20%	0-15%	0-5%
Red Jacket Submersible Turbine Pump (non-AG)	P/N 41014x-xxx	0-20%	0-10%	0-10%
Red Jacket Submersible Turbine Pump (AG)	P/N 41014x-xxx	0-100%	0-100%	0-100%
Red Jacket FX Leak Detector	FXV series	0-20%	0-15%	0-20%

Jeff Kappler
 ATG Product Manager